

RoHS
Compliant



Features

- Our pink antistatic bags are blow-molded with anti static additives from LDPE and LLDPE
- Soft texture and flexible
- Surface resistance of $10^8 \sim 10^{11} \Omega$
- Static release time is >2 secs

Pink anti static bags have the ability to dissipate a static charge to ground preventing static charge building up on the package or device. The material is also antistatic and will not charge up when rubbed against other materials.


Note, these bags have no shielding ability. A static field or discharge occurring outside the bag will penetrate the bag and damage electronics inside.

Additional Notes

Recommend that all of our pink anti static bags be used within 2 years from the date of manufacture. Store this product in its original packaging in a climate-controlled environment where temperature ranges from 21°C to 23°C and relative humidity is 45% to 50%.

Configuration(s):

Bags are offered with a single seal or bottom fold, extruded from a PE tube. The bags are provided with our standard artwork.



Standard Bag Artwork:

Pink antistatic bags are produced with the following sample artwork as standard.



Test Conditions

The following results were taken under the following environmental test conditions: Temperature: 22°C / Humidity: 46%

Item:	Test Standard:	Result:
Film Composition	N/A	LDPE
Film Thickness	Micron Meter	75 micron ($\pm 8\%$) (where applicable)
Melt Index	GB3682	2.1 g/10min
Surface Resistivity	GB3682	$<10^{10} \Omega/\text{sq}$

Pink Antistatic Bag

multicompPRO

Item:	Test Standard:	Result:
Water Absorption Rate	GB/96-04-10	0.5%
Density	GB 1033	0.92 g/cm
Tensile Strength	GB/96-04-10	MD: 32.01 MPa TD: 33.75 MPa
Breaking Elongation Rate	GB/96-04-10	MD: 1200% TD: 685%
Friction Coefficient	GB/96-04-10	Outer Surface: 0.09 Us Inner Surface: 0.08 Ud
Static Dissipation	SJ/T10694-1996	<2 Secs
Appearance	GB/96-04-10	Translucent Sheet (No powder and oil)
Size	GB/96-04-10	Thickness: ±10% Length: ±3mm Width: ±3mm

Test Conclusion:

The pink antistatic LDPE bag is tested accordant with the relevant test standard and requirements.

Test Item:	Test Method:	Measured Equipment(s):	MDL:
Lead (Pb)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Cadmium (Cd)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Mercury (Hg)	IEC 62321:2008 Ed.1 Sec.7	ICP-OES	2mg/kg
Hexavalent Chromium (Cr(VI))	IEC 62321:2008 Ed.1 Annex C	UV-Vis	2mg/kg
Polybrominated Biphenyls (PBBs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg

Note:

The bags are ADD compliant, therefore reserve the right to ship thicker bags from time to time to accommodate ADD import duty tariffs.

Part Number Table

Description	Part Number
Pink Antistatic Bag 300 Gauge / 75 Micron, 508mm×609.6mm, PK100	001-0076

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO